XT Series 30



Your recycling needs. Our grinding solutions.

Granulators dedicated to scraps recovery from rigid or flexible extrusion for small sprues or heavy moulds, also suitable for second step grinding of pre-crushed pieces.

The granulators of this series, thanks to the special design of the grinding chamber, are also widely used for an immediate and safe inline grinding of film and trims.



Access without tools to the parts subject to the ordinary maintenance. Moving on castors.



Grinding chamber in 550HV antiwear execution; hopper opening by gas cylinder.





Integrated electric control panel. Safety devices and circuit in compliance with EEC Directives.



Rotary discs integral with the rotor and containment rings; bench adjustment of rotating and fixed knives. Scissors cutting configuration.



Grinding chamber water cooling; screen surface equal to approximately 50% of knives rotation length.

XT Series 30

FEATURES XT 3530

Feeding opening (mm): 350 x 300 Nr. rotating / fixed knives: 3 / 2 Rotor speed (RPM): 535 Rotor diameter (mm): 260

Motor (kW): 7,5 Weight (kg): 650

Standard screen (mm): 7 - 9

Indicative throughput (kg/hr): 150 ÷ 220

FEATURES XT 5030

Feeding opening (mm): 500 x 300 Nr. rotating / fixed knives: 3 / 2 Rotor speed (RPM): 535 Rotor diameter (mm): 260

Motor (kW): 11 Weight (kg): 750

Standard screen (mm): 7 - 9

Indicative throughput (kg/hr): 200 ÷ 320

FEATURES XT 7030


Feeding opening (mm): 700 x 300 Nr. rotating / fixed knives: 3 / 2 Rotor speed (RPM): 535 Rotor diameter (mm): 260

Motor (kW): 11 Weight (kg): 1000

Standard screen (mm): 7 - 9

Indicative throughput (kg/hr): 300 ÷ 400

DIMENSIONS




	А	В	С
XT 3530	850	340	520
XT 5030	1000	490	670
XT 7030	1200	690	870

OPTIONAL

- A) Knives and screen in antiwear execution
- B) Soundproof rigid flap
- C) Hopper for pipes and sheets
- D) Not soundproof version
- E) Hopper for trims
- F) Aphonic tunnel for conveyor belt
- G) Level control
- H) Discharge for power supply
- I) Discharge with auger screw*
- L) Discharge with suction group on board
- M) Discharge with suction group not on board (* available only for 3530 and 5030)

CHAMBER SECTION: XT SERIES



ACCESSORIES

